

Garant

**Carbide boring bar E.. SVJBR 142°, for indexable inserts VB., right-hand,
Shank Ø / insert size: 25/16mm**


Order data

Order number	261112 25/16
GTIN	4062406398033
Item class	21T

Technical description

ISO code toolholder	E25S SVJBR/L 16
Pack of insert screws	269028 8
Head length L_1	44 mm
Minimum pre-drill $\varnothing D_{\min}$	28 mm
Clamping height L_2	24 mm
Neck width L_4	16.5 mm
Insert size	16 mm
suitable indexable insert	VB.. 1604..
Overall length L	250 mm
Setting angle κ	142 degrees
Centre offset L_3	4.6 mm
Shank $\varnothing D_s$	25 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8×D
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 8	269028 8
-----------------------------	----------