

Garant

Carbide boring bar E.. SVJBL 142°, for indexable inserts VB.., left-hand, Shank Ø / insert size: 20/11mm


Order data

Order number	261113 20/11
GTIN	4062406398057
Item class	21T

Technical description

suitable indexable insert	VB.. 1103..
Setting angle κ	142 degrees
Minimum pre-drill $\varnothing D_{\min}$	24 mm
Pack of insert screws	269028 7
Centre offset L_3	2 mm
ISO code toolholder	E20S SVJBR/L 11
Insert size	11 mm
Overall length L	250 mm
Head length L_1	38 mm
Clamping height L_2	19 mm
Neck width L_4	11 mm
Shank $\varnothing D_s$	20 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8×D
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
-----------------------------	----------