

Garant

HSS boring bar AH.. SDQCL 107,5°, for indexable inserts DC., left-hand, Shank Ø / insert size: 8/07mm


Order data

| | |
|--------------|---------------|
| Order number | 260329 8/07 |
| GTIN | 4062406401078 |
| Item class | 21T |

Technical description

| | |
|--|-----------------|
| Setting angle κ | 107.5 degrees |
| Minimum pre-drill $\varnothing D_{\min}$ | 12 mm |
| Clamping height L_2 | 7 mm |
| ISO code toolholder | AH08K SDQCR/L07 |
| Pack of insert screws | 269028 7 |
| suitable indexable insert | DC.. 0702.. |
| Overall length L | 125 mm |
| Head length L_1 | 20 mm |
| Insert size | 7 mm |
| Centre offset L_3 | 8 mm |
| Shank $\varnothing D_s$ | 8 mm |
| Standard | Works standard |
| Application type | left-hand |
| Boring depth up to | 5×D |
| Tool material | HSS |
| Through-coolant | yes |

| | |
|-----------------|-------------------------------|
| Application | Internal longitudinal turning |
| Type of product | Boring Bar |

Accessories

| | |
|-----------------------------|----------|
| Set of insert screws Type 7 | 269028 7 |
|-----------------------------|----------|