

Garant

HSS boring bar AH.. SDUCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 8/07mm



Order data

Order number	260332 8/07
GTIN	4062406401085
Item class	21T

Technical description

Overall length L	125 mm
Pack of insert screws	269028 7
Setting angle κ	93 degrees
Clamping height L_2	7 mm
ISO code toolholder	AH08K SDUCR/L07
Minimum pre-drill $\varnothing D_{\min}$	13.5 mm
Overhang L_1	40 mm
Insert size	7 mm
suitable indexable insert	DC.. 0702..
Centre offset L_3	7.5 mm
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500