

Garant

**HSS boring bar AH.. SDUCL 93°, for indexable inserts DC., left-hand, Shank
Ø / insert size: 8/07mm**


Order data

Order number	260333 8/07
GTIN	4062406401092
Item class	21T

Technical description

Overall length L	125 mm
Clamping height L ₂	7 mm
Centre offset L ₃	7.5 mm
Minimum pre-drill Ø D _{min}	13.5 mm
Pack of insert screws	269028 7
suitable indexable insert	DC.. 0702..
ISO code toolholder	AH08K SDUCR/L07
Overhang L ₁	40 mm
Insert size	7 mm
Setting angle κ	93 degrees
Shank Ø D _s	8 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500