

Garant
Master Turn steel boring bar helical flutes A.. SCLCR 95°, for indexable inserts CC., right-hand, Shank Ø / insert size: 8/06mm

Order data

Order number	260030 8/06
GTIN	4062406575731
Item class	21T

Technical description

Head length L_1	20 mm
Pack of insert screws	269028 7
Centre offset L_3	5 mm
Overall length L	100 mm
Minimum pre-drill $\varnothing D_{\min}$	10 mm
suitable indexable insert	CC.. 0602..
Shank $\varnothing D_s$	8 mm
Insert size	6 mm
Clamping height L_2	7 mm
ISO code toolholder	A08H SCLCR/L06
Series	GARANT Master
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar