

Garant
Master Turn steel boring bar helical flutes A.. SCLCR 95°, for indexable inserts CC., right-hand, Shank Ø / insert size: 25/09mm

Order data

Order number	260030 25/09
GTIN	4062406575786
Item class	21T

Technical description

Head length L_1	43 mm
suitable indexable insert	CC.. 09T3..
Series	GARANT Master
Shank $\varnothing D_s$	25 mm
Pack of insert screws	269028 8
Overall length L	200 mm
Minimum pre-drill $\varnothing D_{min}$	27 mm
Centre offset L_3	13.5 mm
Clamping height L_2	23 mm
ISO code toolholder	A25R SCLCR/L09
Insert size	9 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar