

Garant
Master Turn steel boring bar helical flutes A.. SCLCL 95°, for indexable inserts CC., left-hand, Shank Ø / insert size: 12/06mm

Order data

Order number	260031 12/06
GTIN	4062406576714
Item class	21T

Technical description

Pack of insert screws	269028 7
Centre offset L_3	7 mm
suitable indexable insert	CC.. 0602..
Insert size	6 mm
Head length L_1	24.3 mm
Minimum pre-drill $\varnothing D_{\min}$	14 mm
Shank $\varnothing D_s$	12 mm
Series	GARANT Master
Overall length L	140 mm
Clamping height L_2	11 mm
ISO code toolholder	A12L SCLCR/L06
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar