

Garant
Master Turn steel boring bar helical flutes A.. SCLCL 95°, for indexable inserts CC., left-hand, Shank Ø / insert size: 25/09mm

Order data

Order number	260031 25/09
GTIN	4062406576745
Item class	21T

Technical description

Pack of insert screws	269028 8
Shank Ø D _s	25 mm
Clamping height L ₂	23 mm
Overall length L	200 mm
suitable indexable insert	CC.. 09T3..
Head length L ₁	43 mm
ISO code toolholder	A25R SCLCR/L09
Insert size	9 mm
Minimum pre-drill Ø D _{min}	27 mm
Series	GARANT Master
Centre offset L ₃	13.5 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar