

Garant
Master Turn steel boring bar helical flutes A.. SCLCL 95°, for indexable inserts CC., left-hand, Shank Ø / insert size: 25/12mm

Order data

Order number	260031 25/12
GTIN	4062406576752
Item class	21T

Technical description

Insert size	12 mm
Overall length L	200 mm
Pack of insert screws	269028 9
Minimum pre-drill Ø D _{min}	27 mm
Clamping height L ₂	23 mm
Head length L ₁	43 mm
Shank Ø D _s	25 mm
Series	GARANT Master
suitable indexable insert	CC.. 1204..
Centre offset L ₃	13.5 mm
ISO code toolholder	A25R SCLCR/L12
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar