

**Garant**
**Master Turn steel boring bar helical flutes A.. SDUCL 93°, for indexable inserts DC., left-hand, Shank Ø / insert size: 10/07mm**

**Order data**

Order number	260337 10/07
GTIN	4062406576820
Item class	21T

**Technical description**

Series	GARANT Master
Centre offset $L_3$	7 mm
Clamping height $L_2$	9 mm
Head length $L_1$	20 mm
suitable indexable insert	DC.. 0702..
Minimum pre-drill $\varnothing D_{\min}$	13 mm
Pack of insert screws	269028 7
Overall length L	125 mm
Insert size	7 mm
ISO code toolholder	A10K SDUCR/L07
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar