

**Garant**
**Master Turn steel boring bar helical flutes A.. SDUCR 93°, for indexable inserts DC., right-hand, Shank  $\varnothing$  / insert size: 12/07mm**

**Order data**

Order number	260336 12/07
GTIN	4062406576776
Item class	21T

**Technical description**

suitable indexable insert	DC.. 0702..
Shank $\varnothing$ D <sub>s</sub>	12 mm
Centre offset L <sub>3</sub>	8 mm
Overall length L	140 mm
Pack of insert screws	269028 7
Head length L <sub>1</sub>	25 mm
Minimum pre-drill $\varnothing$ D <sub>min</sub>	15 mm
ISO code toolholder	A12L SDUCR/L07
Insert size	7 mm
Series	GARANT Master
Clamping height L <sub>2</sub>	11 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar