

Garant
Master Turn steel boring bar helical flutes A.. SDUCL 93°, for indexable inserts DC., left-hand, Shank Ø / insert size: 16/07mm

Order data

Order number	260337 16/07
GTIN	4062406576844
Item class	21T

Technical description

Shank Ø D _s	16 mm
Clamping height L ₂	15 mm
Centre offset L ₃	10 mm
ISO code toolholder	A16Q SDUCR/L07
Overall length L	180 mm
Minimum pre-drill Ø D _{min}	19 mm
Head length L ₁	28 mm
Pack of insert screws	269028 7
suitable indexable insert	DC.. 0702..
Insert size	7 mm
Series	GARANT Master
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar