

Garant
Master Turn steel boring bar helical flutes A.. SDUCL 93°, for indexable inserts DC., left-hand, Shank Ø / insert size: 12/07mm

Order data

Order number	260337 12/07
GTIN	4062406576837
Item class	21T

Technical description

Minimum pre-drill Ø D_{min}	15 mm
Pack of insert screws	269028 7
Insert size	7 mm
suitable indexable insert	DC.. 0702..
Centre offset L_3	8 mm
Head length L_1	25 mm
Clamping height L_2	11 mm
Series	GARANT Master
ISO code toolholder	A12L SDUCR/L07
Shank Ø D_s	12 mm
Overall length L	140 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar