

**Garant**

**Master Turn steel boring bar helical flutes A.. SDUCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 16/11mm**


**Order data**

Order number	260336 16/11
GTIN	4062406576790
Item class	21T

**Technical description**

Overall length L	180 mm
Series	GARANT Master
suitable indexable insert	DC.. 11T3..
Minimum pre-drill $\varnothing D_{\min}$	23 mm
ISO code toolholder	A16Q SDUCR/L11
Centre offset $L_3$	14 mm
Pack of insert screws	269028 8
Head length $L_1$	28 mm
Shank $\varnothing D_s$	16 mm
Insert size	11 mm
Clamping height $L_2$	15 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar