

**Garant**

**Master Turn steel boring bar helical flutes A.. SDUCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 10/07mm**


**Order data**

Order number	260336 10/07
GTIN	4062406576769
Item class	21T

**Technical description**

Centre offset $L_3$	7 mm
Shank Ø $D_s$	10 mm
suitable indexable insert	DC.. 0702..
Head length $L_1$	20 mm
Series	GARANT Master
Pack of insert screws	269028 7
Insert size	7 mm
ISO code toolholder	A10K SDUCR/L07
Clamping height $L_2$	9 mm
Minimum pre-drill Ø $D_{min}$	13 mm
Overall length $L$	125 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar