

Garant

Master Turn steel boring bar helical flutes A.. SDUCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 20/11 mm


Order data

Order number	260336 20/11
GTIN	4062406576806
Item class	21T

Technical description

Series	GARANT Master
Head length L_1	36 mm
ISO code toolholder	A20R SDUCR/L11
Clamping height L_2	18 mm
Centre offset L_3	13 mm
suitable indexable insert	DC.. 11T3..
Shank Ø D_s	20 mm
Insert size	11 mm
Overall length L	200 mm
Pack of insert screws	269028 8
Minimum pre-drill Ø D_{min}	25 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar