

Garant
Master Turn steel boring bar helical flutes A.. SDUCL 93°, for indexable inserts DC., left-hand, Shank Ø / insert size: 20/11mm

Order data

Order number	260337 20/11
GTIN	4062406576868
Item class	21T

Technical description

Clamping height L_2	18 mm
Series	GARANT Master
Pack of insert screws	269028 8
Overall length L	200 mm
Head length L_1	36 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Insert size	11 mm
Shank $\varnothing D_s$	20 mm
Centre offset L_3	13 mm
ISO code toolholder	A20R SDUCR/L11
suitable indexable insert	DC.. 11T3..
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar