

**Garant**
**Master Turn steel boring bar helical flutes A.. SDUCL 93°, for indexable inserts DC., left-hand, Shank Ø / insert size: 25/11mm**

**Order data**

Order number	260337 25/11
GTIN	4062406576875
Item class	21T

**Technical description**

Pack of insert screws	269028 8
suitable indexable insert	DC.. 11T3..
Insert size	11 mm
Series	GARANT Master
Head length L <sub>1</sub>	40 mm
ISO code toolholder	A25R SDUCR/L11
Centre offset L <sub>3</sub>	16 mm
Shank Ø D <sub>s</sub>	25 mm
Overall length L	200 mm
Clamping height L <sub>2</sub>	23 mm
Minimum pre-drill Ø D <sub>min</sub>	31 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar