

Garant**Master Turn steel boring bar helical flutes A.. SDUCL 93°, for indexable inserts DC., left-hand, Shank Ø / insert size: 16/11mm****Order data**

Order number	260337 16/11
GTIN	4062406576851
Item class	21T

Technical description

Series	GARANT Master
Overall length L	180 mm
Pack of insert screws	269028 8
Head length L ₁	28 mm
Shank Ø D _s	16 mm
ISO code toolholder	A16Q SDUCR/L11
Centre offset L ₃	14 mm
suitable indexable insert	DC.. 11T3..
Insert size	11 mm
Minimum pre-drill Ø D _{min}	23 mm
Clamping height L ₂	15 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar