

**Garant**

**Master Turn steel boring bar helical flutes A.. SDQCR 107,5°, for indexable inserts DC., right-hand, Shank Ø / insert size: 12/07mm**


**Order data**

Order number	260330 12/07
GTIN	4062406576899
Item class	21T

**Technical description**

Head length L <sub>1</sub>	25 mm
Centre offset L <sub>3</sub>	8 mm
ISO code toolholder	A12L SDQCR/L07
Series	GARANT Master
Pack of insert screws	269028 7
suitable indexable insert	DC.. 0702..
Shank Ø D <sub>s</sub>	12 mm
Overall length L	140 mm
Clamping height L <sub>2</sub>	11 mm
Minimum pre-drill Ø D <sub>min</sub>	15 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

