

**Garant**

**Master Turn steel boring bar helical flutes A.. SDQCL 107,5°, for indexable inserts DC., left-hand, Shank Ø / insert size: 25/11mm**


**Order data**

Order number	260331 25/11
GTIN	4062406576998
Item class	21T

**Technical description**

Series	GARANT Master
ISO code toolholder	A25R SDQCR/L11
Minimum pre-drill Ø $D_{min}$	31 mm
Shank Ø $D_s$	25 mm
Pack of insert screws	269028 8
suitable indexable insert	DC.. 11T3..
Overall length L	200 mm
Head length $L_1$	40 mm
Clamping height $L_2$	23 mm
Centre offset $L_3$	16 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

