

Garant

Master Turn steel boring bar helical flutes A.. SDQCR 107,5°, for indexable inserts DC., right-hand, Shank Ø / insert size: 16/07mm


Order data

Order number	260330 16/07
GTIN	4062406576905
Item class	21T

Technical description

Series	GARANT Master
suitable indexable insert	DC.. 0702..
Minimum pre-drill $\varnothing D_{\min}$	19 mm
Overall length L	180 mm
Pack of insert screws	269028 7
Head length L ₁	28 mm
ISO code toolholder	A16Q SDQCR/L07
Clamping height L ₂	15 mm
Centre offset L ₃	10 mm
Shank $\varnothing D_s$	16 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

