

**Garant**

**Master Turn steel boring bar helical flutes A.. SDQCR 107,5°, for indexable inserts DC., right-hand, Shank Ø / insert size: 20/11mm**


**Order data**

Order number	260330 20/11
GTIN	4062406576929
Item class	21T

**Technical description**

suitable indexable insert	DC.. 11T3..
Clamping height $L_2$	18 mm
Shank Ø $D_s$	20 mm
Centre offset $L_3$	13 mm
Minimum pre-drill Ø $D_{min}$	25 mm
ISO code toolholder	A20R SDQCR/L11
Series	GARANT Master
Overall length L	200 mm
Pack of insert screws	269028 8
Head length $L_1$	36 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

