

Garant

Master Turn steel boring bar helical flutes A.. SDQCL 107,5°, for indexable inserts DC., left-hand, Shank Ø / insert size: 12/07mm


Order data

Order number	260331 12/07
GTIN	4062406576950
Item class	21T

Technical description

Head length L ₁	25 mm
Overall length L	140 mm
Pack of insert screws	269028 7
Series	GARANT Master
Shank Ø D _s	12 mm
Clamping height L ₂	11 mm
ISO code toolholder	A12L SDQCR/L07
Centre offset L ₃	8 mm
suitable indexable insert	DC.. 0702..
Minimum pre-drill Ø D _{min}	15 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

