

Garant

Master Turn steel boring bar helical flutes A.. SDQCL 107,5°, for indexable inserts DC., left-hand, Shank Ø / insert size: 10/07mm


Order data

Order number	260331 10/07
GTIN	4062406576943
Item class	21T

Technical description

suitable indexable insert	DC.. 0702..
ISO code toolholder	A10K SDQCR/L07
Centre offset L ₃	7 mm
Head length L ₁	20 mm
Overall length L	125 mm
Pack of insert screws	269028 7
Clamping height L ₂	9 mm
Shank Ø D _s	10 mm
Series	GARANT Master
Minimum pre-drill Ø D _{min}	13 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

