

Garant

Master Turn steel boring bar helical flutes A.. SDQCR 107,5°, for indexable inserts DC., right-hand, Shank Ø / insert size: 16/11mm


Order data

Order number	260330 16/11
GTIN	4062406576912
Item class	21T

Technical description

Clamping height L_2	15 mm
Minimum pre-drill $\varnothing D_{\min}$	23 mm
Series	GARANT Master
Head length L_1	28 mm
Centre offset L_3	14 mm
Shank $\varnothing D_s$	16 mm
Overall length L	180 mm
Pack of insert screws	269028 8
ISO code toolholder	A16Q SDQCR/L11
suitable indexable insert	DC.. 11T3..
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

