

Garant

Master Turn steel boring bar helical flutes A.. SDQCL 107,5°, for indexable inserts DC., left-hand, Shank Ø / insert size: 20/11mm


Order data

Order number	260331 20/11
GTIN	4062406576981
Item class	21T

Technical description

ISO code toolholder	A20R SDQCR/L11
Head length L ₁	36 mm
Shank Ø D _s	20 mm
Pack of insert screws	269028 8
Minimum pre-drill Ø D _{min}	25 mm
Clamping height L ₂	18 mm
Overall length L	200 mm
suitable indexable insert	DC.. 11T3..
Series	GARANT Master
Centre offset L ₃	13 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

