

Garant

Master Turn steel boring bar helical flutes A.. SDQCL 107,5°, for indexable inserts DC., left-hand, Shank Ø / insert size: 16/07mm


Order data

Order number	260331 16/07
GTIN	4062406576967
Item class	21T

Technical description

Centre offset L_3	10 mm
Clamping height L_2	15 mm
Overall length L	180 mm
suitable indexable insert	DC.. 0702..
Shank Ø D_s	16 mm
Pack of insert screws	269028 7
ISO code toolholder	A16Q SDQCR/L07
Head length L_1	28 mm
Series	GARANT Master
Minimum pre-drill Ø D_{min}	19 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

