

Garant

Carbide quick-change boring bar E.. SCLCR 95°, for indexable inserts CC., right-hand, Shank Ø DS / insert size: 8/03mm


Order data

Order number	268110 8/03
GTIN	4062406583965
Item class	21P

Technical description

Setting angle κ	95 degrees
Insert size	3 mm
Pack of insert screws	269028 13
ISO code toolholder	E08X SCLCR/L03
Head length L_1	26 mm
Minimum pre-drill $\varnothing D_{\min}$	5 mm
Shank $\varnothing D_s$	8 mm
Overall length L	57 mm
Centre offset L_3	2.5 mm
Neck width L_4	4 mm
suitable indexable insert	CC.. 0301..
Standard	DIN 8024
Application type	right-hand
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar

Accessories

Set of insert screws Type 13

269028 13