

Garant

Carbide quick-change boring bar E.. SCLCL 95°, for indexable inserts CC., left-hand, Shank dia. DS / insert size: 8/03mm


Order data

Order number	268111 8/03
GTIN	4062406583972
Item class	21P

Technical description

Insert size	3 mm
Minimum pre-drill $\varnothing D_{\min}$	5 mm
Head length L_1	26 mm
Setting angle κ	95 degrees
Centre offset L_3	2.5 mm
ISO code toolholder	E08X SCLCR/L03
Shank $\varnothing D_s$	8 mm
Overall length L	57 mm
Pack of insert screws	269028 13
suitable indexable insert	CC.. 0301..
Neck width L_4	4 mm
Standard	DIN 8024
Application type	left-hand
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar

Accessories

Set of insert screws Type 13

269028 13