



Lever lock toolholder set, right-hand, Shank size: 32mm



Order data

| | |
|--------------|---------------|
| Order number | 255120 32 |
| GTIN | 4062406609412 |
| Item class | 29W |

Technical description

| | |
|---------------------------------|-------------------------------|
| Head length L ₁ | 40 mm |
| ISO code toolholder | PCLNR 3232P16; PDJNR 3232P15 |
| Shank size | 32 mm |
| Spare part | 259981 9 |
| Overall length L | 170 mm |
| Functional width L ₄ | 40 mm |
| suitable indexable insert | CN.. 1606..; DN.. 1506.. |
| Standard | Works standard |
| Application type | right-hand |
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

Spare parts set for lever lock toolholder Type 8

259981 8