

Garant

Clamping toolholder SDJCL 93°, for indexable inserts DC., left-hand, Shank / insert size: 16/07mm



Order data

Order number	260309 16/07
GTIN	4062406602253
Item class	21T

Technical description

Shank size	16 mm
Overall length L	100 mm
Functional width L ₄	20 mm
Insert size	7 mm
ISO code toolholder	SDJCR/L 1616H07
suitable indexable insert	DC.. 0702..
Head length L ₁	22 mm
Pack of insert screws	269028 22
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15