

**Garant**
**Master Turn steel boring bar helical flutes A.. STFC, for indexable inserts TC., right-hand, Shank  $\varnothing$  / insert size: 10/11mm**

**Order data**

Order number	260932 10/11
GTIN	4062406677244
Item class	21T

**Technical description**

Series	GARANT Master
ISO code toolholder	A10K STFCR/L11
Overall length L	125 mm
Setting angle $\kappa$	90 degrees
Pack of insert screws	269028 7
Centre offset $L_3$	6.2 mm
Shank $\varnothing D_s$	10 mm
Head length $L_1$	22 mm
Clamping height $L_2$	9 mm
Insert size	11 mm
suitable indexable insert	TC.. 1102..
Minimum pre-drill $\varnothing D_{min}$	12 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar