

Garant
Master Turn steel boring bar helical flutes A.. STFC, for indexable inserts TC., right-hand, Shank \varnothing / insert size: 16/11mm

Order data

Order number	260932 16/11
GTIN	4062406677268
Item class	21T

Technical description

Head length L_1	31 mm
Centre offset L_3	9.2 mm
Setting angle κ	90 degrees
Shank $\varnothing D_s$	16 mm
suitable indexable insert	TC.. 1102..
Overall length L	180 mm
Minimum pre-drill $\varnothing D_{min}$	18 mm
Insert size	11 mm
Pack of insert screws	269028 7
ISO code toolholder	A16Q STFCR/L11
Clamping height L_2	15 mm
Series	GARANT Master
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar