

Garant

Master Turn steel boring bar helical flutes A.. STFC, for indexable inserts TC., right-hand, Shank \varnothing / insert size: 12/11mm


Order data

Order number	260932 12/11
GTIN	4062406677251
Item class	21T

Technical description

Head length L_1	24.3 mm
Shank $\varnothing D_s$	12 mm
Pack of insert screws	269028 7
Overall length L	140 mm
Minimum pre-drill $\varnothing D_{min}$	14 mm
suitable indexable insert	TC.. 1102..
Series	GARANT Master
Clamping height L_2	11 mm
Insert size	11 mm
ISO code toolholder	A12L STFCR/L11
Centre offset L_3	7.2 mm
Setting angle κ	90 degrees
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar