

Garant

Master Turn steel boring bar helical flutes A.. STFC, for indexable inserts TC.., right-hand, Shank \varnothing / insert size: 20/11mm


Order data

Order number	260932 20/11
GTIN	4062406677275
Item class	21T

Technical description

Series	GARANT Master
ISO code toolholder	A20R STFCR/L11
Insert size	11 mm
Centre offset L_3	11.1 mm
Overall length L	200 mm
Head length L_1	36 mm
suitable indexable insert	TC.. 1102..
Shank $\varnothing D_s$	20 mm
Clamping height L_2	18 mm
Setting angle κ	90 degrees
Minimum pre-drill $\varnothing D_{min}$	22 mm
Pack of insert screws	269028 7
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar