



## Top jaws set, 3 pieces, for chuck type: 170



### Order data

|              |               |
|--------------|---------------|
| Order number | 313725 170    |
| GTIN         | 4067263151890 |
| Item class   | 32R           |

### Description

#### Version:

**Precision milled** slots and serration, **not burnished**.

#### Material:

Quality product made of 16MnCr5.

#### Suitable for:

**Heavy-duty chucks** from Schunk, Röhm and other heavy-duty chuck manufacturers.

#### Optional extras:

T-nuts No. 313505 – 313605.

#### Note:

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

### Technical description

|                       |        |
|-----------------------|--------|
| Length L              | 72 mm  |
| Slot width D          | 12 mm  |
| for chuck type        | 170 mm |
| Hole centre spacing a | 15 mm  |
| Width B               | 32 mm  |
| for thread DIN 912    | M10    |
| Height H              | 40 mm  |

|                          |                                   |
|--------------------------|-----------------------------------|
| Bore spacing b           | 20 mm                             |
| suitable for colour code | Schunk heavy-duty chucks and jaws |
| Type of product          | Heavy-duty lathe chuck jaws       |