



Top jaws set, 3 pieces, for chuck type: 254



Order data

Order number	313725 254
GTIN	4067263152316
Item class	32R

Description

Version:

Precision milled slots and serrations, **not burnished**.

Material:

Quality product made of 16MnCr5.

Suitable for:

Heavy-duty chucks from Schunk, Röhm and other heavy-duty chuck manufacturers.

Optional extras:

T-nuts No. 313505 – 313605.

Note:

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

Technical description

Hole centre spacing a	30 mm
Slot width D	16 mm
Bore spacing b	30 mm
for chuck type	254 mm
for thread DIN 912	M12
Width B	50 mm
Height H	45 mm

Length L	110 mm
suitable for colour code	Schunk heavy-duty chucks and jaws
Type of product	Heavy-duty lathe chuck jaws