



## Top jaws set, 3 pieces, for chuck type: 315



### Order data

Order number	313725 315
GTIN	4067263152330
Item class	32R

### Description

#### Version:

**Precision milled** slots and serration, **not burnished.**

#### Material:

Quality product made of 16MnCr5.

#### Suitable for:

**Heavy-duty chucks** from Schunk, Röhm and other heavy-duty chuck manufacturers.

#### Optional extras:

T-nuts No. 313505 – 313605.

#### Note:

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

### Technical description

Bore spacing b	30 mm
Slot width D	18 mm
for chuck type	315 mm
Length L	130 mm
Hole centre spacing a	40 mm
for thread DIN 912	M14
Width B	50 mm

Height H	50 mm
suitable for colour code	Schunk heavy-duty chucks and jaws
Type of product	Heavy-duty lathe chuck jaws