

**Garant**

**Steel boring bar A... SVOCL, for indexable inserts VC., left-hand, Shank  $\varnothing$  / insert size: 8/05mm**

**Order data**

Order number	261379 8/05
GTIN	4062406710781
Item class	21T

**Technical description**

Setting angle $\kappa$	140 degrees
Head length $L_1$	15 mm
Overall length $L$	80 mm
ISO code toolholder	A08F SVOCR/L05
Centre offset $L_3$	3 mm
Minimum pre-drill $\varnothing D_{\min}$	8 mm
suitable indexable insert	VC.. 0501..
Insert size	5 mm
Shank $\varnothing D_s$	8 mm
Clamping height $L_2$	7.5 mm
Pack of insert screws	269028 26
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar