

**Garant**

**Steel boring bar A... SVOCL, for indexable inserts VC., left-hand, Shank  $\varnothing$  / insert size: 12/07mm**

**Order data**

Order number	261379 12/07
GTIN	4062406710804
Item class	21T

**Technical description**

Minimum pre-drill $\varnothing D_{\min}$	13 mm
Centre offset $L_3$	6.5 mm
Setting angle $\kappa$	140 degrees
suitable indexable insert	VC.. 0702..
Clamping height $L_2$	11 mm
ISO code toolholder	A12L SVOCR/L07
Head length $L_1$	24 mm
Insert size	7 mm
Overall length L	140 mm
Shank $\varnothing D_s$	12 mm
Pack of insert screws	269028 27
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar