

Garant

Steel boring bar A... SVOCR, for indexable inserts VC., right-hand, Shank \varnothing / insert size: 20/11mm


Order data

Order number	261378 20/11
GTIN	4062406710774
Item class	21T

Technical description

Clamping height L_2	19 mm
Insert size	11 mm
Centre offset L_3	11 mm
suitable indexable insert	VC.. 1103..
Shank $\varnothing D_s$	20 mm
Setting angle κ	140 degrees
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{min}$	24 mm
ISO code toolholder	A20Q SVOCR/L11
Head length L_1	40 mm
Overall length L	180 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar