

Garant

Steel boring bar A... SVOCL, for indexable inserts VC., left-hand, Shank \varnothing / insert size: 10/07mm


Order data

Order number	261379 10/07
GTIN	4062406710798
Item class	21T

Technical description

suitable indexable insert	VC.. 0702..
Setting angle κ	140 degrees
Centre offset L_3	5.5 mm
Head length L_1	22 mm
Overall length L	100 mm
ISO code toolholder	A10H SVOCR/L07
Clamping height L_2	9 mm
Shank $\varnothing D_s$	10 mm
Insert size	7 mm
Pack of insert screws	269028 27
Minimum pre-drill $\varnothing D_{\min}$	11 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar