

Garant

Steel boring bar A... SVOCR, for indexable inserts VC., right-hand, Shank \varnothing / insert size: 12/07mm


Order data

Order number	261378 12/07
GTIN	4062406710750
Item class	21T

Technical description

Overall length L	140 mm
Head length L ₁	24 mm
Minimum pre-drill $\varnothing D_{\min}$	13 mm
Insert size	7 mm
Centre offset L ₃	6.5 mm
Shank $\varnothing D_s$	12 mm
ISO code toolholder	A12L SVOCR/L07
Clamping height L ₂	11 mm
Pack of insert screws	269028 27
suitable indexable insert	VC.. 0702..
Setting angle κ	140 degrees
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar