

**Garant**

**Steel boring bar A... SVOCL, for indexable inserts VC., left-hand, Shank  $\varnothing$  / insert size: 20/11mm**


**Order data**

Order number	261379 20/11
GTIN	4062406710828
Item class	21T

**Technical description**

Pack of insert screws	269028 7
suitable indexable insert	VC.. 1103..
Shank $\varnothing$ D <sub>s</sub>	20 mm
Minimum pre-drill $\varnothing$ D <sub>min</sub>	24 mm
Setting angle $\kappa$	140 degrees
Clamping height L <sub>2</sub>	19 mm
Overall length L	180 mm
Centre offset L <sub>3</sub>	11 mm
Head length L <sub>1</sub>	40 mm
Insert size	11 mm
ISO code toolholder	A20Q SVOCR/L11
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar