

**Garant**

**Steel boring bar A... SVOCL, for indexable inserts VC., left-hand, Shank  $\varnothing$  / insert size: 16/11mm**

**Order data**

Order number	261379 16/11
GTIN	4062406710811
Item class	21T

**Technical description**

Overall length L	150 mm
ISO code toolholder	A16M SVOCR/L11
Setting angle $\kappa$	140 degrees
suitable indexable insert	VC.. 1103..
Minimum pre-drill $\varnothing D_{\min}$	22 mm
Pack of insert screws	269028 7
Shank $\varnothing D_s$	16 mm
Insert size	11 mm
Centre offset $L_3$	9 mm
Clamping height $L_2$	15 mm
Head length $L_1$	35 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar