

Garant

Carbide boring bar E... SVOCL, for indexable inserts VC.., left-hand, Shank \varnothing / insert size: 8/05mm


Order data

Order number	261377 8/05
GTIN	4062406710859
Item class	21T

Technical description

Centre offset L_3	3 mm
suitable indexable insert	VC.. 0501..
Head length L_1	26 mm
Overall length L	80 mm
Shank $\varnothing D_s$	8 mm
Minimum pre-drill $\varnothing D_{min}$	8 mm
Clamping height L_2	7.5 mm
Setting angle κ	140 degrees
Insert size	5 mm
ISO code toolholder	E08F SVOCR/L05
Pack of insert screws	269028 26
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar