

Garant
Master Turn steel boring bar helical flutes A.. STFC, for indexable inserts VB., left-hand, Shank \varnothing / insert size: 12/11mm

Order data

Order number	260933 12/11
GTIN	4062406711030
Item class	21T

Technical description

Setting angle κ	90 degrees
Centre offset L_3	7.2 mm
Pack of insert screws	269028 7
Clamping height L_2	11 mm
Shank $\varnothing D_s$	12 mm
Series	GARANT Master
Insert size	11 mm
suitable indexable insert	TC.. 1102..
Overall length L	140 mm
Minimum pre-drill $\varnothing D_{min}$	14 mm
Head length L_1	24.3 mm
ISO code toolholder	A12L STFCL/L11
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar