

Garant
Master Turn steel boring bar helical flutes A.. STFC, for indexable inserts VB., left-hand, Shank \varnothing / insert size: 16/11mm

Order data

Order number	260933 16/11
GTIN	4062406711047
Item class	21T

Technical description

Overall length L	180 mm
Shank \varnothing D _s	16 mm
Insert size	11 mm
Minimum pre-drill \varnothing D _{min}	18 mm
Clamping height L ₂	15 mm
Centre offset L ₃	9.2 mm
suitable indexable insert	TC.. 1102..
Pack of insert screws	269028 7
Series	GARANT Master
ISO code toolholder	A16Q STFCR/L11
Head length L ₁	31 mm
Setting angle κ	90 degrees
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar